



Diode Laser Hair Removal Machine KM 2024 Exchange 6 Size With 3000W High Power Handle

Our Product Introduction

Basic Information

- Place of Origin: Shandong, China
- Brand Name: km
- Model Number: 360D
- Price: \$4,599.00/sets 1-2 sets




Product Specification

- Warranty: 2 Years
- After-sales Service Provided: Other, Field Maintenance And Repair Service, Online Support, Free Spare Parts, Video Technical Support, Field Installation, Commissioning And Training
- Type: STANDING
- Feature: Acne Analysis, Pigmentation Analysis, Skin Wrinkle Analysis, Detect Skin Moisture
- Application: For Home Use, For Commercial
- Name: Laser Hair Removal System 755nm 808nm 1064nm 3 Waves Titanium
- Spot Size: 12*20mm 15*27mm 12*35mm 14*14mm
- Laser Wavelength: 808nm-810nm/808+755+1064nm Option
- Laser Bars: 6-16 Laser Bars Option
- Languages Option: English, Spanish, Portuguese, Turkish...
- Screen: 15 Inch Color Touch Screen
- OEM/ODM Service: YES, professional



for more products please visit us on wfkmdz.com

More Images



Our Advantages


KM LASER Machine Upgrade points

- 1) 360 plus uses **6D TIP technology**.
- 2) **Six different light spots** are automatically recognized by the 6 in 1 system on one handle
- 3) Automatically adjusted to the treatment parameters of the corresponding TIP, Avoid burns or lack of energy
- 4) **Double-row lasers, Energy utilization rate is over 95%**
- 5 **With hair follicle analyzer** that can see changes in hair follicles






SUITABLE FOFR ALL PARTS OF THE BODY




With hair follicle analyzer that can see changes in hair follicles



Intelligent AI Recognition for different spot size

When you change the spot size, the system automatically adjusts the parameters



Intelligent software parameters reset automatically

I believe you are a professional buyer, please read this form carefully

vs!!!	KM LASESR	OTHERS
Identify	Intelligent AI recognition technology (System automatically identifies the installed spot and automatically adjusts to the treatment parameters of the corresponding TIP)	No automatic recognition
Risk	Intelligently adjust parameters to avoid burns or insufficient energy	It is easy to get burned or lack of energy when adjusting the light spot
Light loss	Passed the American Tracepro optical experimental data test, the light energy transmittance is 96.5!!	Failed the light decay test
Transmission	Wireless transmission, no problem of poor contact	Wired transmission is prone to poor contact or no data transmission
Fixed way	Magnetic force + fixing pin + curved edge teeth, no light leakage and stronger	JUST Magnetic, The light source easily diverges, Easy to deform
Chip	USA Coherent imported laser bar WITH certification	NO certification
Energy utilization rate	Energy utilization rate is over 95%	Energy utilization rate is only 60%
Certification	MDSAP ,Medical CE , TGA, TUV	NO MDSAP, TGA

Passed the American Tracepro optical experimental data test, the light energy transmittance is 96.5 %

USA Coherent imported laser bar WITH Certification

Magnetic force + fixing pin + curved edge teeth, handle head no light leakage and stronger



Golden laser bars

Original place of raw material

All of our laser bars have unique code, by the code, we can check the original place of the laser bars, the test report etc. Each laser bar have it's quality test and make sure client can use without problem.

SI 9161 Rev AA

2022.12.9
low (10/11/14)

Part Used: 22100-21
POM
SOP: 201016

Customer Name: Coherent (Beijing) Commercial Co Ltd
Draw number: 177011

Description: UM73AUM8-50(1) Laser 730nm 100mW

Lot#	Lot Number	Qty	UM73AUM8-50(1) Control	UM73AUM8-50(1) Control	UM73AUM8-50(1) Control	Trace SN	Top IMA	Vop = 2.4V	Top Thickness (mm)	Trace bar material included	
8.1	18122.1	40	1004	112	Yes	Yes	31101	40.24	1.54	110	Yes
	18122.1	73	1104	101	Yes	Yes	31148	41.9	1.53	110	Yes
	18122.1	230	1101	111	Yes	Yes	31124	40.41	1.51	109	Yes

Total Qty: 140

Manufacturing Test Data Sheet **COHERENT**

SI-80-100.05-40-90-A Serial# 722078 SC721 012421 03:00:15 PM
Rev. # 5.5.2

Test: S80 Part number: 126276
Notes: Rev. # 5.5.1.1

PVI characteristics

Frequency, Hz	500.00
Pulse Width, uSec	500.00
Pep, W	100.00
Ith, A	17.00
Ith, A	14.43
Slope Eff. W/A	1.24
Eff. @Ith, %	13.76
Max Eff. %	55.88
Rs, mOhms	3.6
VGS@I, V	1.84
VTV	1.69
T, C	21.0
Peak wavelength, nm	866.19
Control wavelength, nm	867.79
FWHM, nm	2.07
FWHM% Energy, nm	2.95
FWHM% Max, nm	3.54
FWHM% Max, nm	2.89
T, C	25.00

Spectrum

Part Used: 20100-21
POM
SOP: 201040

Customer Name: Coherent (Beijing) Commercial Co Ltd
Draw number: 188019

Description: UM73AUM8-50(1) Laser 730nm 100mW

Lot#	Lot Number	Qty	UM73AUM8-50(1) Control	UM73AUM8-50(1) Control	UM73AUM8-50(1) Control	Trace SN	Top IMA	Vop = 2.4V	Top Thickness (mm)	Trace bar material included
3.1	17706.1	17	161.2	Yes	Yes	31203	41.7	1.57	110	Yes
	17706.1	181	168.2	Yes	Yes	31207	41.04	1.56	110	Yes

Total Qty: 200



Why choose KM diode laser hair removal machine?

*Much stable and higher powerful new golden welding laser module with USA Coherent imported laser bar WITH certification. It can shot about **500 million times** .

***Double water filters**, only change filters per 6 months and 1 year. And some old filters in some machines need change filter every month. Save much maintainance cost and times for you .


*New Italy Bluid-o-tech imported water pump replaced Chinese pump with better cooling system and more quiet duiring treatment. Those obvious difference will be found when your customers compare with some machines with Chinese water pump.

*Japan TDK Six way power supply replaced four way power supply, much higher and stable output.

*TEC cooling system, can control water temperature by yourself to keep 808 diode laser machine running continuously within 24 hours even in Summer. Same function as your A/C in your house .

*Various power laser modules for your option , 300W 500W 600W 800W 1000W 1200W 1600W ... (6bars 10basr 12bars 16bars)

*Single 808 wave, 755nm/808nm/1064nm double wave and triple wave for option.



755+808+1064nm Platinum Style Technology.

The 3 waves works in the same handle at the same time:

755nm for **white skin**(fine, golden hair)

808nm for **yellow/neutral skin**

1064nm for **black**(black hair)



Before



Before



After



After

PERMANENT REDUCTION IN HAIR REGROWTH



Week 1-3



Week 4-5



Week 6-7



After Week 8

Laser type	Diode laser
Laser wavelength	808nm or 3 wave 755&808&1064nm
Spot size	12*12 mm ² , 12*20 mm ² , 15*27mm ² , 12*35 (optional)
Pulse width	1-400 ms (adjustable), 300ms, 200ms(optional)
Energy	1-160 J/cm ² (adjustable) 280J 360J(optional)
Frequency	1-10 Hz(adjustable)
Language	English, Spanish, Italian, German, French, Turkish or any other language as requested
Skin type	I-VI skin type
Update system	USB update
Rent System	Optional
12 Display	12.4"/15inch color touch LCD display
Laser module power	600W/800W/1000w/1200W/1600W
Cooling	water + air + semiconductor + A/C+TEC big cooler part
Voltage	110V/220V±20V, 50/60Hz


F*A Support for querying 510K-codes on the official website

KM LASER Since 2009,

the leading manufacturer of aesthetic machines in the industry, focusing on high quality and high technology of equipment

Device Classification Name	powered laser surgical instrument
510(k) Number	K182924
Device Name	Diode Laser Treatment System
Applicant	Weifang KM Electronics Co., LTD No. 7999 Health East Street, High-Tech District Weifang, CN 261000
Applicant Contact	Andy Pang
Correspondent	Weifang KM Electronics Co., LTD No. 7999 Health East Street, High-Tech District Weifang, CN 261000
Correspondent Contact	Andy Pang
Regulation Number	878.4810
Classification Product Code	GEX
Date Received	10/19/2018
Decision Date	04/15/2019
Decision	Substantially Equivalent (SESE)
Regulation Medical Specialty	General & Plastic Surgery
510k Review Panel	General & Plastic Surgery
Summary	Summary
Type	Traditional
Reviewed by Third Party	No
Combination Product	No

We have **MDSAP AND TUV ISO 13485** .Certified by **27 EU countries, Brazil, New Zealand, Japan, Canada, and the United States**





Machine Screen

OEM /ODM

* 6 skin types

* Any language could be added

* Logo could be added for free * 12.0 inch touch screen* With male and female , 6 skin styles to choose from ,easy to operate



Company Profile



DUST-FREE WORKSHOP



DUST-FREE WORKSHOP OF LASER MODULE ASSEMBLY FOR LONG SERVICE LIFE

Weifang KM Electronics Co., Ltd. 14 years factory

2 years warranty

102 countries, 60000+ customers * 755+808+1064nm Ice Cooling Diode Laser Series,

Multi-function series 2 in 1, 3 in 1, 6 in 1 series, Elight series, Q Switch ND YAG laser series, * Fat lossing : RF series ,Cavitation and so on.

Weifang KM Electronics Co., Ltd. is a professional factory focusing on development of beauty devices for 14 years. All the products are with

CE/ISO certification ,suitable for world market , mainly used on North America , South America , Europe, our aim is on the development of beauty equipment, Pursuit of higher product quality, Making your business easier!

FACTORY FLOOR



5 PRODUCTION LINE FOR MACHINES ASSEMBLE AND HANDPEICE ASSEBLE



MACHINE DELIVERY



Authoritative Certificates

* TUV medical CE approved 93/42/EEC standard

* TUV ISO 13485:2016 newest standard and more strict for production line inspection .There is few supplier get Medical CE and ISO13485 from TUV in China market now

triple trio laser 755 810 1064 nm 808nm hair removal machine

3 wavelengths diode laser 755 808 1064nm Titanium hair removal machine machine

KM *Health/Beauty* Weifang KM Electronics Co., Ltd.

☎ 13606464486

✉ sales@wfkmdz.com

🌐 wfkmdz.com

D3-H-0, D3-H-17, D3-H-18, No. 7999, East Health Street, Yongchun Community, Qingchi Street, High-Tech Zone, Weifang, Shandong, China