



## 25khz 40khz Vacuum Cavitation System Desktop Weight Loss Slimming Machine

Our Product Introduction

for more products please visit us on [wfkmdz.com](http://wfkmdz.com)

### Basic Information

- Place of Origin: China
- Certification: MDRCE
- Price: \$1,780.00/sets >=1 sets
- Packaging Details: Aluminum box&Carton box



### Product Specification

- Target Area: Body, Face, Legs/Arms, Neck/Throat, Hands
- Type: Desktop
- Feature: Weight Loss, Skin Tightening, Cellulite Reduction
- Plugs Type: AU, Other, UK, EU, US, CN, JP, Za, It
- Application: For Commercial
- After-sales Service Provided: Free Spare Parts, Online Support, Field Installation, Commissioning And Training, Video Technical Support, Other, Field Maintenance And Repair Service
- Warranty: 2 Years
- Machine Key Words: Vacuum Cavitation System
- Operation System: Ultrasonic+RF+Vacuum
- Cavitation Frequency: 40khz,33khz,28khz
- Cavitation Energy: 3W/CM2
- RF Output Mode: Monopolar,Bipolar,Tripolar



### More Images



## Product Description

2021 Weight Loss Slimming Machine Equipment With 25khz 40khz Vacuum Cavitation System



### 3 in 1 cavitation 25khz 40khz Application:

1. Weight loss, ultrasonic cellulite reduction, body slimming, fat removal
2. Lipolysis break up lipocytes and body shaping together.
3. Tighten skin, promote the skin elasticity by Monopolar, bipolar and tripolar radio frequency
4. Remove wrinkle, face lifting, eye bag removal, face, chin, cheek treatment
5. Anti-cellular oxidation, aging.
6. Body shaping, body sculpting, body massage

### Handpiece development history:

#### Handpieces Improved From Time To Time

We will continue with the innovation of our products, keeping our products more advanced, more nice

2007 style, rough work ugly appearance, fragile, easily into the gel	2008 style, workmanship has improved, made by aluminum, heavy, easy conductivity	2009 style, meticulous workmanship made by aluminum, easy conductivity	2012 European and American popular styles, userfriendly design, not easily into the gel, suitable for different size of the palm of your hand, feel comfortable, not easy to conductive

#### Different Treat Head Available for choosing (optional)

Cavitation	Vacuum	Bipolar RF With Five Tip
big bipolar rf	small bipolar rf	Lipolysis
Big tripolar rf	Small tripolar rf	Cooling Bipolar RF

### Cavitation Machine Treatment Area:



Super advanced control system:

### Control system

CPU using AFM core control technology with linux system.

1. Update the system
2. Repair the system
3. Connect the computer mouse

USB firm update by yourself needn't return the machines back to factory!

Five-point calibration touch screen

Two different operation mode :  
Touch and mouse

True color LCD touch screen

Circuit diagram  
Schematic diagram

Multi language for option:

### Professional software design, easy to operate





**KM Unique Slimming Technology**

## Core Technology Different — Cavitation handpieces

<p><b>KM</b> Humanization design Europe and America style</p>  <p>Ultrasound Cavitation Monopolar RF</p>	 <p>Ultrasound+RF</p>
<p>Other factory's</p>  <p>Only Ultrasound</p>	 <p>Only Ultrasound</p>







KM cavitation combine Cavitation and Monopolar RF two kinds of technique to one handpieces, the two functions can work at same time. improve effect 200%, reduces the treatment time "1+1>2"

## Core Technology Different — Vacuum handpieces

<p><b>KM</b> Humanization design Europe and America style</p>  <p>Vacuum Tripolar RF Electrodes LD Cold laser</p>	 <p>Vacuum Tripolar RF + Cold Laser</p>
<p>Other factory's</p>  <p>Only Vacuum</p>	 <p>Only Vacuum</p>

KM vacuum combine Vacuum, Tripolar RF, Cold laser three kinds of technique to one handpieces, all the function can work at same time. improve effect 150% , reduces the treatment time "1+1+1>3"

## Core Technology Different — Tripolar RF handpieces

<p><b>KM</b> Humanization design Europe and America style</p>  <p>A B C</p>	 <p>True Tripolar RF</p> 
<p>Other factory's</p>  <p>A B C</p>	 <p>Fault Tripolar RF</p> 

True and false Tripolar RF identification method : True tripolar RF three electrodes send Rf energy in turn, false tripolar RF there's two head is hot at same time, because false tripolar Rf infact is bipolar RF. the effect is far from true tripolar RF.

**Rent system for option:**

## Remote rent system



RENT program can help the distributors do the "RENT business" very convenient, no need for the IC card and RF card to easily rent their own instruments

### Parameter:

Tripolar RF	6MHZ RF
Cavitation frequency	40K HZ
Cavitation max output:	100W
Vacuum Pressure	1000Kpa
Monopolar rf	1Mhz(Output frequency),50J(Maximum output power)
Operative Interface	8.4 Inch TFT true color LCD touch screen
Electrical Sourc	110V/220V±10V,AC 50/60Hz
Warranty	1-2 Years

## Fast Treatment Result



### KM Cavitation Machine advantage:

- 1.Combine the new low frequency ultrasound Cavitation, lipolysis, RF, Vacuum, 650nmLaser four tehnology in one machine, achieve the slimming plus tighten skin perfect effect one time.
- 2.7 System: cavitation+monopolar+bipolar+tripolar+lipolysis+vacuum+laser
- 3.USB updating Technology,easy to save and print data.
- 4.No pain, no invasive,painless,suitable to all people who suffering fat problems
- 5.No skin color requirements, widely application
- 6.Large color touch screen with clear treatment parameters, friendly operation
- 7.Solve the multiple proble areas: waistline, abdomen, back, buttocks & thigh areas, arms & underarms
- 8.Professional vacuum pump, best result traceless, no rebound, long-lasting result!
- 9.No consume, inner system achieve to international CE standard

### Why Choose Us

A: All kinds of Certification  
(CE,ISO Quality certificate,Free Sales Certificate,SGS,BV,Medical Equipment Production Permission)

## Authoritative certification Quality assurance



B: Professional Production Line

(Every production steps have strict rule and every worker only do one step.It is easy for us to control the quality)

## Production line and design department



C: Professional Testing Tools:

(All these tools are used for the machine testing during production and after production.Make sure all parameters are specific)

## Professional Testing Tools



D: Firm Package

(All of our inside package with foam shape which was made according the machine shell, the outside is aluminium box and carton box)

E: Fast Delivery

(All of our machines was sent by DHL,UPS,TNT,Air Cargo,clients can receive the machine within 1 week)

F:Comprehensive Training

We have user manual, Doctor Training Manual, DVD and online service to teach you how to use machine

G: Our hottest selling machine all over the world

Those products are hottest sold to beauty salon , dermatology hospital and medical institute all over the world.

At the same time, our professional beauty machine make great profits for them, praised by users.

Welcome to contact Weifang KM Company!!

Contact: Jessie

WhatsApp/Ph: 0086-15095095081

Skype: chinakmbeauty

**KM** | *Health/Beauty* **Weifang KM Electronics Co., Ltd.**

 13606464486  [sales@wfkmdz.com](mailto:sales@wfkmdz.com)  [wfkmdz.com](http://wfkmdz.com)

D3-H-0, D3-H-17, D3-H-18, No. 7999, East Health Street, Yongchun Community, Qingchi Street, High-Tech Zone, Weifang, Shandong, China