Commercial Q Switched Laser Tattoo Removal Machine 1064nm 532nm 755nm

Basic Information

Place of Origin: Shandong, China

Brand Name: OEMMinimum Order Quantity: 1

• Price: \$6,980.00/sets 1-2 sets

Packaging Details: boxDelivery Time: 1-7daysSupply Ability: 100sets



Product Specification

Production Name:
 Q Switched Laser Tattoo Removal Machine

Q-Switch: Yes

Laser Type: Nd: Yag LaserStyle: Stationary

• Type: Laser, Picosecond Laser Tattoo

• Feature: Pigment Removal, Dark Circles, Skin

Tightening, Pore Remover, Whitening, Acne Treatment, Skin Rejuvenation, Pigmentation Correctors, Tattoo Removal, LIP PLUMPER

Application: For Commercial

After-sales Service Provided:
 Free Spare Parts, Online Support, Video Technical Support, Field Installation.

Technical Support, Field Installation, Commissioning And Training, Field Maintenance And Repair Service

Warranty: 2 Years

• Wavelength: 1064nm/532nm/755nm(optional)

• Pulse Width: 500ps-900ps



More Images









Product Description

500ps-900ps Pulse Width Q-Switched Yag Laser Hair Removal Machine For Tattoo Removal

Products Description







Hair Removal Advantage

- No need to apply cold gel, no need to shave, improve the efficiency of treatment
- > 50-80 J Energy, fast hairremoval
- ➤ 6ns pulse width, No pain, The smaller the pulse width, the better treatment

Treatment Theropy:

Picosecond laser uses very short pulse output mode, instead of thermal effect, by the principle of light mechanical shock wave, pigment is "shattered" into finely granular via focused energy, are more likely to be absorbed by the body metabolism. Picosecond laser will be to minimize the side effects of thermal effect, can achieve the goal of almost solve all kinds of pigment spots, is better than traditional laser spot whitening effect

Applications for picosecond laser:

HAIR REMOVAL

Chloasma, coffee spots, freckles, sunburn, age spots, nevus of ota,

Acne scars,


Skin whitening, fine lines removal,

All colors of tattoo removal



Hair Removal Advantage

A.<u>No need to apply cold gel,</u> no need to shave, improve the efficiency of treatment B<u>.50-80 J Energy</u>,fast hair removal C.6ns pulse width, No pain,The smaller the pulse width, the better treatment






- 1-20mm adjustable
- 4-5ms pulse width, 50-80 J fast hair removal Any color tattoo removal
- 1)1-10mm adjustable,1-8m for freckles & tattoo removal

2)15mm,20mm for hair removal
3)585nm 680nm for blue &green &colorfu tattoo removal

Focus Array Lens



The Focus Array Lensis indicated for the treatment of acne scars and wrinkles,


also could improve skin texture as rejuvenation. The treatment could stimulate the production of new collagen and elastic fibers, which result in reducing fine lines and pores size,

elastic fibers, increasing skin elasticity and improving skin condition.

Luxury design new

Various treatment handles

Free choice of suitable treatment head



Luxury design new

Test energy

Test energy more accurately







Vegs

Old Picosecond machine use Coherent Test energy Our NEW picosecond machine use VEGS test energy

1.2j single light double rod laser ,6ns pulse width,φ7 φ8 It's a circle of light spots with clear boundaries

Luxury design new

1.2j single light double rod laser , 6ns pulse width, φ 7 φ 8

clear boundaries



- red line clear boundaries
- Blue cross blurred border



It's a circle of light spots with clear boundaries

Pico Second Laser Advantages

Quality assured



HIGH ENERGY & SHOT PULSE DURATION

The power emit in trillions of a second to skin tissue, which can explore the pigment into much more small pieces than traditional Q:switch laser. The pigment pieces can be absorbed more easily and faster



MINIMAL RISK

Since the pulse duration has been reduced thousand of time, less damage of skin is realized. The treatment is more safe and less pain



FAST

For tattoo removal, usually 6-8 treatment is necessary by Traditional Q:switch laser. With pico second laser, only 3-4 treatment is needed only for completely removal.



HIGH PERFORMANCE

Completely removal of tattoo and pigment can be reached with Pico second technology Luxury design new

Free choice of various software

Software can be customized













Laser type Electro-Optic Q-switched Nd:YAG Solid State Laser

Wavelength 1064nm, 532nm,(755nm,585nm,650nm)

Controller 10.4 inch Color Touch Display Screen

MAX 1500mJ (1064nm); MAX800mJ (532nm)

Single-Q Energy MAX 2500mJ (1064nm); MAX1500mJ (532nm) Double-Q Energy

Long pulse mode (1064nm): Max.3000mJ

laser mode Single-Q / double Q/ long pulse

Beam profile Flat-top mode

Power 2000W

Width of pulses ≤ 6ns (Q-Switched mode)

300 us (Long pulse mode)

Frequency 1-10(15HZ)

Diameter of spot 2-10mm adjustable

Beam of light transmission 7 articular-arm of light guide transmitting, transmission power is

more than 90%

Indicator of aiming light red semiconductor aiming light, wavelength 650nm(Red Diode

Laser(On, Off, Blinking Available))

Cooling manner Closed-off water circulation + air

Program language English, German, franch,,,, according your required

Dimension of machine 88*32*83 cm

Dimension of package 112*54*100 cm

N.W. 70kg G.W. 120 kg

Packing wooden case and Aluminum Box

Voltage AC230V / 110V

Company Profile

WHY CHOOSE US

Professional OEM, ODM service for Ice laser machine

1)In stock 12 hours delivery

- 2) Print any color you want for your machine, make it be your and your client's favorite.
- 3) Print your logo on the machine shell and add it to the system as a welcome interface. Make it exclusive in the world.
- 4) Add any language into the machine system, according to you and your client's requirements.
- 5) Add the Remote Rental System into the machine to do lease business.
- 6) Design an exclusive machine shell for you, form your own brand in the market.
- 7) Design a new interface and system of machine, making it most convenient for you and your clients.
- 8) Develop the newest technology to satisfy you and your client's demand.aser machine hair removal made in US hair removal ice hair removal machine laser diode 3 waves beauty machine




* TUV ISO 13485:2016 newest standard and more strict for production line inspection

* There is few supplier get Medical CE and ISO13485 from TUV in China market now

- * KM was founded in 2009, and we employ more than 100 highly valued team members. Every year, our team participates in beauty machine exhibitions to actively learn about the demands of the beauty market from the customers and other industry professionals themselves. This allows us added knowledge to design more competitive products
- * KM has many medical and production certifications around the world, including (TUV) CE, (TUV) ISO 13485:2016, new type machine shell patent certification, Import and export license, Medical equipment production enterprise license and we have been awarded a High-tech enterprise certificate in China.
- * KM's enterprise vision is customer-oriented and we are dedicated to providing end customers with high quality and cost efficient beauty equipment. KM continues to work hard for customers in order to become a world famous supplier of beauty machines and medical equipment





Packing & Delivery





13606464486

sales@wfkmdz.com

wfkmdz.com

D3-H-0, D3-H-17, D3-H-18, No. 7999, East Health Street, Yongchun Community, Qingchi Street, High-Tech Zone, Weifang, Shandong, China