



1064nm 532nm 1320nm Nd Yag Laser Equipment Portable For Skin Whitening

Our Product Introduction

for more products please visit us on wfkmdz.com

Basic Information

- Place of Origin: Shandong, China
- Brand Name: Healthy&Beauty
- Certification: ISO9001
- Model Number: KM-L-100B
- Price: \$1,300.00/sets 1-5 sets
- Packaging Details: outside:carton box
inside:aluminium box



Product Specification

- Q-Switch: NO
- Laser Type: Nd: Yag Laser
- Style: Portable
- Type: Laser
- Feature: Acne Treatment, Anti-Puffiness, Pigment Removal, Pigmentation Correctors, Tattoo Removal
- Application: For Commercial
- After-sales Service Provided: Free Spare Parts, Video Technical Support, Field Installation, Commissioning And Training, Online Support
- Warranty: 2 Years
- Colour: Red,blue,slivery,pink,white,and So On
- Languages: 24 Different Languages Can Choose
- Output Energy: 1~ 2000mJ(Adjustable)
- Frequency: 1-10Hz



More Images



Product Description

Air Water Temperature Control Cooling System NO Q-Switch Laser Tattoo Removal Device

Welcome distributors from all over the world. Welcome to visit our factory at any time. We will offer the best quality machine and most professional training

q switch nd yag laser tattoo removal black doll treatment machine

Would you want to get quick reply within 24 hours online ?


please contact with me directly Tel/WhatsApp/Wechat number : **+8618754414717**

KM[®]



Working Principle of nd yag laser tattoo removal machine

Laser emitted by the system has a strong penetration ability which allows it to reach the deep layer of dermis. The pigment particles absorb the light energy and explode sharply, burst into the tiny pieces, thus diminish the color density and get rid of it. So the appliance can effectively do away with mutant pigmentations and vascular tissue based on undamaged ambient tissue. This is called 'Selective heat absorption' principle in medical field.



Advanced unique technology of nd yag laser tattoo removal machine

1. Painless treatment, no injury to skin and hair follicle, no risk of scarring, no side-effect
2. Imported stone Q-switch cassette mechanism, the entire solid laser, without replacing Q-switch.
3. Instantaneous blasting high laser technology, international standard of production, technical test strictly.
4. Have the alert device for conk out of water level, water temp, water flux and refrigeration.
5. Remember system and Reset function ease for medical or esthetic institutions to decrease cost.
6. Colorful touch display, which is easy and visual to operate, excellent cooling system

Widely applications of nd yag laser tattoo removal machine

1. **532nm wavelength:** get rid of freckles, eyebrow tattoo, failed eye line tattoo, tattoo, lips line, pigment, telangiectasia in shallow red, brown and pink and etc. light color
2. **1064nm wavelength:** get rid of freckles and yellow brown spot, eyebrow tattoo, failed eye line tattoo, tattoo, Birthmark and Nevus of Ota, pigmentation and age spot, nevus in black and blue, scarlet red, deep coffee and etc. deep color.
3. **1320nm wavelength:** shrink pores removal, pblackhead removal, skin tightening and whitening, skin rejuvenation, wrinkle removal



Handle:

1) fixed 1064nm&532nm ,adjustable 1064nm&532nm(adjust 1-9mm) for tattoo removal, nevus removal, etc. 1320nm for skin whitening.

2)Adopt imported nd yag laser bar, can reach 1,000,000 shots.

This machine is equipped with 650nm red light arm, make sure to do the accurate therapy

What's the difference between 3 wavelength?

Q-Switch nd yag laser machine has 3 tips with 3 different wavelength:

1. 1064nm:

- Mainly for black or other dark color tattoo removal.
- Freckle, nevus ... removal

2. 532nm:

- Mainly for red or other colorful tattoo removal.

3. 1320nm / Carbon tip:

- For carbon treatment / skin rejuvenation treatment.



• **Lightweight** hand piece never makes you tired.

• Both hand piece & foot pedal can emit light.

• With infrared guide light. On / Off adjustable



Handpiece



Specification of nd yag laser tattoo removal machine

Laser type	Q-Switched ND YAG laser
Wavelength	1320nm&1064nm & 532nm
Spot diameter	1-8mm adjustable
Cooling system	wind + closed water circulation cooling
Display	8.4 Inch big touch color display
Output power	1800W
Pulse energy	0-1600MJ Pulse width:5-10ns
Frequency	1-10HZ(Adjustable)
Voltage	220V/110V, 50/60HZ

Why Choose Us?

France Schneider parts



Easy broken



Others

With hose protection
Italy import hose



Without protection
Hose will damage after long time using.



Others

Special design for Laser Rod
ensures longer lifespan and
stable energy



Old type combination which is
easy leak energy



Others

Unique protective device for
laser lamp which ensures longer
lifespan



No device protect laser lamp
efficient operation

Others

Electro Magnetic Compatibility



Without EMC
Machine and energy are
not stable.

Others

Italian water pump, high flow rate.




Low flow rate pump



Others

Aiming beam on / off optional
More convinient for treatment



No Aiming beam switch button
Even no aiming beam

(Aiming beam=Guid light)

Others

What is Q Switched ND Yag Laser Machine?

It is a machine that can **remove**:

- ✓ Colorful tattoo
- ✓ Permanent make up
- ✓ Pigmentation
- ✓ Freckle
- ✓ Nevus
- ✓ And Skin rejuvenation

Contrast photos taken by doctor:



- 1) Professional cooling system
- 2) Advanced CPU technology
- 3) USB updating system
- 4) New treatment system
- 5) Five levels of security protection
- 6) New Rent system

more advanced technical

Five levels of security protection

System self-check: ensure the normal operation of the system

Over-voltage over-current protection function

Reset M Counter	Reset W Counter	Reset R Counter
000123	000345	
Power Checking	Charging Checking	IC Check
YES	YES	NO
Level Checking	Current Checking	Temperature Alarm
	NO	55
Fluorescence Setting	Factory Mode	Workshop Mode
NO	400	NO



Air switch ensure the system can be outaged once electric leakage



Emergency switch ensure the system can be stopped working immediately if any accident



Water flow & temperature switch alarms timely and stop shining when no water, less water, slow flow and high temperature.

Five levels of security protection (air switch, power supply insurance, circuit of explosion-proof capacitor, water switches, temperature probe), To ensure personal and equipment is absolute security

Control system



CPU using ARM core control technology with linux system.

1. Update the system
2. Repair the system
3. Connect the computer mouse



USB free update by yourself, needn't return the machines back to factory!



Five-point calibration touch screen

Two different operation mode :
Touch and mouse




Circuit diagram


Schematic diagram

True color LCD touch screen

Remote rent system



leaseholder



lessee

RENT program can help the distributors do the "RENT business" very convenient, no need for the IC card and RF card to easily rent their own instruments

Following is our professional Active Q Switched nd yag laser machine, please click the picture and get more information.

KM[®]



Our Services

1) Warranty

We provide 2 years long warranty to customers. Lifelong free maintenance.

2) Training

We could offer our customer professional training, ensure every customer own the professional operation knowledge in time, DVD for training or online training directly. No any charge, for free!

3) Professional OEM & ODM Service

As we are a professional beauty machine manufacture in china, we can offer every distributor and dealer the OEM/ODM Service without any design charge, any advice from our customer there is hot welcome!

4) Free logo, language, color design

We can add your logo on the machine screen for free.

We can design your language in the screen for free.

You can choose any color you like for machine.

5) Delivery

We will deliver the machine within 3 days.

We can deliver the goods to all over the world. It takes 3~5 days by DHL door to door.

KM factory show



KM certificates



Our customers



FAQ



Shipping terms



KM | *Health/Beauty* Weifang KM Electronics Co., Ltd.

☎ 13606464486 ✉ sales@wfkmdz.com 🌐 wfkmdz.com

D3-H-0, D3-H-17, D3-H-18, No. 7999, East Health Street, Yongchun Community, Qingchi Street, High-Tech Zone, Weifang, Shandong, China