



## White Shell IPL Laser Hair Removal Machine For Skin Rejuvenation

Our Product Introduction

for more products please visit us on [wfkmdz.com](http://wfkmdz.com)

### Basic Information

- Place of Origin: Shandong, China
- Brand Name: Health&Beauty
- Model Number: KM-IPL-100A
- Minimum Order Quantity: 1
- Packaging Details: box
- Delivery Time: 1-7days
- Supply Ability: 100sets




### Product Specification

- IPL+ RF: NO
- After-sales Service Provided: Online Support, Free Spare Parts, Video Technical Support, Field Maintenance And Repair Service, Field Installation, Commissioning And Training
- Type: IPL
- Feature: Acne Treatment, Blood Vessels Removal, Breast Enhancers, Hair Removal, Pigment Removal, Pigmentation Correctors, Skin Rejuvenation, Skin Tightening, Wrinkle Remover, Anti-Puffiness, Pore Remover, Face Lift
- Application: For Commercial
- Screen: 8.4inch TFT True Color Touch Screen
- Shell Color: White,Gray,Pink,Red ,as You Like
- Language: English,Portuguese,Spanish,Italian,Russian,F Etc
- Power: 1200W



### More Images



## Product Description

Safe 2023 Weifang KM IPL Laser Hair Removal And Skin Rejuvenation Machine In White Shell

### 2023 Weifang KM ipl Laser hair removal ipl skin rejuvenation machine Intense Pulsed Light Depilador




Trolley size: 60cm×45cm×76cm(L\*W\*H)



Machine size: 44cm×32cm×38cm(L\*W\*H)

#### KM intelligent software design



2 treatment modes




Multi language for option



Water flow intelligent detection, dual water temperature intelligent protection



Total shot numbers and shot number per session



Renting system for lease business

#### Applications of IPL machine

1. Smooth wrinkles, face-lifting
2. Deep flecks, epidermis flecks or pigment treating the telangiectasis
3. Promote collagen to grow, strengthen flexibility of skin
4. Acne treatment
5. OPTink the thick pore
6. Removal light-colored or dark and thick extra hair
7. For endogenous pigment: nevus of Ota, coffee spot, age pigment, freckle etc removal
8. For exogenous pigment: tattoo, eyeliner and eyebrow removal
9. Skin whitening
10. Striae gravidarum removal



#### **Application of different sapphire filters**

1. 480nm for vascular lesions and red blood streak treatment.
2. 530nm for skin rejuvenation
3. 560nm for photo rejuvenation, skin tightening, whitening, improving the flexibility of the skin and reduce the wrinkle
4. 590nm for pigmentation and spot removal
5. 640nm for hair removal

### Supper cooling effect

8×40(mm<sup>2</sup>)

12×45(mm<sup>2</sup>)

12×30(mm<sup>2</sup>)

15×50(mm<sup>2</sup>)

**OR**

8×40(mm<sup>2</sup>)

12×45(mm<sup>2</sup>)

12×30(mm<sup>2</sup>)

15×50(mm<sup>2</sup>)

■ The fastest refrigeration

■ Different spot size select according your request

#### **General introduction**

5 Insertable Sapphire Filters! easy to change!

Optional big spot treatment head available:15mm\*50mm,12mm\*30mm

12 kinds of languages such as:German ,English, Spanish, Dutch, Japanese French Portugues

professional and simple two optional models

## Humanized design, different spot sizes



## Professional software design, easy to operate



### Technique Specification of ipl machine

Wavelength:	430/530/560/590/640~1200nm (Standard) 480/520/755~1200nm (Option) 560/585/640~1200nm (Option)
Treat head Spot size	12 x 30mm <sup>2</sup> ; 8x40mm <sup>2</sup> ; 15x50mm <sup>2</sup> (Optional)
Treat head Number	3 Treat Head
Cooling System	Air & Close Water Circuittation & Treatment head with semiconductor cooling temperature adjustable
IPL Light Energy	10~50 J/cm <sup>2</sup> (adjustable)
Pulse Duration	2~15ms (adjustable)
Pulse Sequence	1~15 pulses (adjustable)
Delay Time	5~50 ms (adjustable)
Integrated Skin Cooling	-4degree~ +10degree
Operative Interface	8.4 inch TFT LCD true color touch screen
Outlet Power	2000W
Electrical Source	110V/220V±10V, AC 50/60Hz
Dimension	750*595*1320 (L x W x H)cm

## Professional software design, easy to operate




### Advantages of ipl machine


1. Non-invasive and non-ablative treatment for skin
2. RF energy is suitable for all skin type and all skin tone
3. Significantly less energy required than conventional lasers and IPLs



4. Superior performance and patient comfort with no down time
5. Virtually painless skin tightening technology without surgery
6. Quick and easy handpiece installation
7. With One fixed handpieces for SR and HR
8. Modularized assemble technique and easy for maintenance
9. With 8.4" deluxe touch screen
10. State-of-the-art design



### KM core parts development



### IPL headpiece details

#### Best Quality Handpiece

- 1 100% Germany and USA Import
- 2 Shot Button 100% Import from Japan
- 3 High Quality Sapphire Protection Cover
- 4 SHR Lamp import from USA
- 5 High Quality Shot Counter
- 6 High Quality Sapphire Parts
- 7 100% Import from USA

### Protection System

## Five levels of security protection

System self-check: ensure the normal operation of the system

Over-voltage over-current protection function

Reset HR Counter	Reset SR Counter	Reset WF Counter
000123	000345	
Power Checking	Charging Checking	IC CA300
YES	YES	NO
Level Checking	Current Checking	Temperature down
	NO	55
Fluence Setting	Factory Mode	Watercolor Mode
NO	400	NO



Air switch ensure the system can be outaged once electric leakage



Emergency switch ensure the system can be stopped working immediately if any accident



Water flow&temperture switch alarms timely and stop shining when no water,less water,slow flow and high temperture.

Five levels of security protection (air switch, power supply insurance, circuit of explosion-proof capacitor, water switches, temperature probe), To ensure personal and equipment is absolute security

*Professional production workshop and sales office!*

## Production line and design department



*All kinds of certificate*

## KM factory show



## KM certificates



### Delivery terms:



We are glad to invite you to try our machinery which will bring you much profit. We offer OEM, ODM service for distributors including design the colors, logo, and new cover, software design...

If you have interest in our products, please do not hesitate to send your enquiry.

Best regards from Sandy

## Shipping terms



Weifang KM Electronics Co., Ltd.

Tel: 0086-536-8885352

MB: 0086-13792693152

Skype:km.beauty

KM *Health/Beauty* Weifang KM Electronics Co., Ltd.

13606464486

sales@wfkmdz.com

wfkmdz.com

D3-H-0, D3-H-17, D3-H-18, No. 7999, East Health Street, Yongchun Community, Qingchi Street, High-Tech Zone, Weifang, Shandong, China