



Commercial Settings Cavislim Machine 40khz 33khz 28khz For Breast Enhancers

Our Product Introduction

Basic Information

- Place of Origin: China
- Brand Name: Health&Beauty
- Model Number: KM-RF-U900C
- Price: \$2,099.00/sets 1-9 sets
- Packaging Details: Aluminum box&Carton box
- Supply Ability: 5000 Set/Sets per Year

KM®



Product Specification

- Target Area: Body, Face, Legs/Arms, Neck/Throat, Hands, Head
- Type: STANDING
- Feature: Weight Loss, Breast Enhancers
- Plugs Type: AU, Other, UK, EU, US, CN, JP, Za, It
- Application: For Commercial
- After-sales Service Provided: Free Spare Parts, Online Support, Field Installation, Commissioning And Training, Video Technical Support, Field Maintenance And Repair Service
- Warranty: 2 Years
- ODM&OEM: Yes
- Cavitation Frequency: 40khz,33khz,28khz
- Cavitation Power: 100W
- Cavitation Energy: 3W/CM2
- RF Output Mode: Monopolar,Bipolar,Tripolar

KM®



More Images

KM®



KM®



KM®



for more products please visit us on wfkmdz.com

Product Description

ISO13485 Approved Cavislim Machine Perfect For Breast Enhancers In Commercial Settings

cavitation radiofrecuencia Application:

1. Weight loss, ultrasonic cellulite reduction, body slimming, fat removal
2. Lipolysis break up lipocytes and body shaping together.
3. Tighten skin, promote the skin elasticity by Monopolar, bipolar and tripolar radio frequency
4. Remove wrinkle, face lifting, eye bag removal, face, chin, cheek treatment
5. Anti-cellular oxidation, aging.
6. Body shaping, body sculpting, body massage

cavitation radiofrecuencia Handpiece development history:

Handpieces Improved From Time To Time

We will continue with the innovation of our products, keeping our products more advanced, more nice

			
2007 style, rough work ugly appearance, fragile, easily into the gel	2008 style, workmanship has improved, made by aluminum, heavy, easy conductivity	2009 style, meticulous workmanship made by aluminum, easy conductivity	2012 European and American popular styles, userfriendly design, not easily into the gel, suitable for different size of the palm of your hand, feel comfortable, not easy to conductive

Different Treat Head Available for choosing (optional)


		
Cavitation	Vacuum	Bipolar RF With Five Tip
		
big bipolar rf	small bipolar rf	Lipolysis
		
Big tripolar rf	Small tripolar rf	Cooling Bipolar RF

cavitation radiofrecuencia Treatment Area:





Super advanced control system:

Control system




CPU using AFM core control technology with linux system.

1. Update the system
2. Repair the system
3. Connect the computer mouse







USB to update by yourself, can't return the machines back to factory!



Five-point calibration touch screen

**Two different operation mode :
Touch and mouse**

True color LCD touch screen

Multi language for option:

Professional software design, easy to operate

KM Unique Slimming Technology

Core Technology Different —Cavitation handpieces




KM cavitation combine Cavitation and Monopolar RF two kinds of technique to one handpieces, the two functions can work at same time. improve effect 200%, reduces the treatment time **"1+1>2"**

Core Technology Different —Vacuum handpieces



KM vacuum combine Vacuum, Tripolar RF, Cold laser three kinds of technique to one handpieces, all the function can work at same time. improve effect 150%, reduces the treatment time **"1+1+1>3"**

Core Technology Different —Tripolar RF handpieces



True and false Tripolar RF identification method : True tripolar RF three electrodes send Rf energy in turn, false tripolar RF there's two head is hot at same time, because false tripolar Rf infact is bipolar RF. the effect is far from true tripolar RF.

Rent system for option:

Remote rent system



leaseholder

lessee

RENT program can help the distributors do the "RENT business" very convenient, no need for the IC card and RF card to easily rent their own instruments

cavitation radiofrecuencia Parameter:

Tripolar RF	6MHZ RF
Cavitation frequency	40K HZ
Cavitation max output:	100W
Vacuum Pressure	1000Kpa
Monopolar rf	1Mhz(Output frequency),50J(Maximum output power)
Operative Interface	8.4 Inch TFT true color LCD touch screen
Electrical Sourc	110V/220V±10V,AC 50/60Hz
Warranty	1-2 Years

Fast Treatment Result



cavitation radiofrecuencia advantage:

- 1.Combine the new low frequency ultrasound Cavitation, lipolysis, RF, Vacuum, 650nmLaser four tehnology in one machine, achieve the slimming plus tighten skin perfect effect one time.
- 2.7 System: cavitation+monopolar+bipolar+tripolar+lipolysis+vacuum+laser
- 3.USB updating Technology,easy to save and print data.
- 4.No pain, no invasive,painless,suitable to all people who suffering fat problems
- 5.No skin color requirements, widely application
- 6.Large color touch screen with clear treatment parameters, friendly operation
- 7.Solve the multiple proble areas: waistline, abdomen, back, buttocks & thigh areas, arms & underarms
- 8.Professional vacuum pump, best result traceless, no rebound, long-lasting result!
- 9.No consume, inner system achieve to international CE standard

Why Choose Us

A: All kinds of Certification

(CE,ISO Quality certificate,Free Sales Certificate,SGS,BV,Medical Equipment Production Permission)

Authoritative certification Quality assurance



B: Professional Production Line

(Every production steps have strict rule and every worker only do one step.It is easy for us to control the quality)

Production line and design department



C: Professional Testing Tools:

(All these tools are used for the machine testing during production and after production.Make sure all parameters are specific)

Professional Testing Tools



D: Firm Package

(All of our inside package with foam shape which was made according the machine shell, the outside is aluminium box and carton box)

E: Fast Delivery

(All of our machines was sent by DHL,UPS,TNT,Air Cargo,clients can receive the machine within 1 week)

F:Comprehensive Training

We have user manual, Doctor Training Manual, DVD and online service to teach you how to use machine

G: Our hottest selling machine all over the world

Those products are hottest sold to beauty salon , dermatology hospital and medical institute all over the world.

At the same time, our professional beauty machine make great profits for them, praised by users.

Welcome to contact Weifang KM Company!!

Contact: Jessie

Phone: 0086-15095095081

Skype: chinakmbauty



Weifang KM Electronics Co., Ltd.



13606464486



sales@wfkmdz.com



wfkmdz.com

D3-H-0, D3-H-17, D3-H-18, No. 7999, East Health Street, Yongchun Community, Qingchi Street, High-Tech Zone, Weifang, Shandong, China