



## Hot Selling High Quality Permanent 808 Laser Hair Removal Device to Remove Hair From All Parts of the Body

### Our Product Introduction

#### Basic Information

- Place of Origin: Shandong, China
- Brand Name: KM LASER Health&Beauty
- Model Number: KM diode laser
- Minimum Order Quantity: 1
- Price: \$3,699.00/sets 1-19 sets
- Packaging Details: box
- Delivery Time: 1-7days
- Supply Ability: 100sets



#### Product Specification

- Name: Diode Ice Laser Machine
- Q-Switch: NO
- Laser Type: 808nm Diode Laser
- Style: Stationary
- Type: Laser
- Feature: Skin Tightening, Pore Remover, Anti-Hair Removal, Whitening, Hair Removal, Face Lift, Acne Treatment, Skin Rejuvenation, Diode Laser For Hair Removal 808nm Beauty Machine Depilight
- Application: For Commercial
- After-sales Service Provided: Free Spare Parts, Video Technical Support, Field Installation, Commissioning And Training, Online Support, Field Maintenance And Repair Service
- Warranty: 2 Years
- Beauty Salon Equipment: 50% Discount 3D Diode Lazer For Beauty Products For Women

## Product Description

**810 808nm Ice Diodo Trio 3 Wave Diode Laser The Most Effective Hair Removal Solution**

### How to choose a suitable laser hair removal machine?

**We are Weifang KM electronics Co.,Ltd, a manufacturer of beauty laser machine since 2009.**

How should you choose a good supplier for the best machine, best price and timely after service?

After doing a lot of research at beauty exhibition, in the E-commerce website, or by google , all manufacturer tell you that their machine quality is best, their price is best. But for you, how do you tell the difference between the different suppliers?

To be honestly, that is not really enough time in this two minutes video for me to compare between different suppliers. But I am going to give you 4 things which you should consider

1. Don't compare a machine by it's specification parameters, it will be a misleading if you are not familiar with the machine technical. Normally, they generally think that a high power, high number on the specification means that machine is wonderful. But do you really think the machine meet your request?
2. Don't buy a very cheaper machine, don't buy a overpriced machine. Buy a machine in middle price with good value. I will tell you how choose a good price machine.
3. Don't buy machine from trading company. As we know, aesthetic beauty machines need timely and professional after service, need good training. A real manufacturer can give you technical support and online training, they can also help you to solve the machine problem with their engineer. I will tell you how to find a real manufacturer
4. Don't buy machine which don't have Medical CE, F\*A, MDL etc approval. Do you know why?



### **KM LASER Machine Upgrade points**

- 1) 360 plus uses **6D TIP** technology.

- 2)**Six different light spots** are automatically recognized by the 6 in1 system on one handle  
 3)Automatically adjusted to the treatment parameters of the corresponding TIP,Avoid burns or lack of energy  
 4)**Double-row lasers,Energy utilization rate is over 95%**


vs!!!	KM LASESR	OTHERS
Identify	Intelligent AI recognition technology (System automatically identifies the installed spot and automatically adjusts to the treatment parameters of the corresponding TIP)	No automatic recognition
Risk	Intelligently adjust parameters to avoid burns or insufficient energy	It is easy to get burned or lack of energy when adjusting the light spot
Light loss	Passed the American Tracepro optical experimental data test, the light energy transmittance is 96.5!!	Failed the light decay test
Transmission	Wireless transmission, no problem of poor contact	Wired transmission is prone to poor contact or no data transmission
Fixed way	Magnetic force + fixing pin + curved edge teeth, no light leakage and stronger	JUST Magnetic,The light source easily diverges,Easy to deform
Chip	USA Coherent imported laser bar WITH certification	NO certification
Energy utilization rate	Energy utilization rate is over 95%	Energy utilization rate is only 60%
Certification	MDSAP ,Medical CE , TGA, TUV	NO MDSAP,TGA



When you change the spot size, the system automatically adjusts the parameters



Passed the American Tracepro optical experimental data test, the light energy transmittance is 96.5%




## Single row-laser 100w/bar




500-2000W Can choice	500W	600W	800W	1000W	1200W	1400W	1600W	1600W	2000W
Bars	5	6	8	10	12	12	16	18	20
Pitch/mm	2.94	2.94	2.94	2.94	2.94	2.14	2.14	2.14	1.96
Pulse Width	300	300	300	260	260	150	150	130	120
Energy/J	150	180	240	260	312	210	240	240	240
Number of people treated	👤 x5	👤 x7	👤 x10	👤 x12	👤 x13	👤 x14	👤 x16	👤 x18	👤 x24
Comfort Level	❤️ x2	❤️ x2	❤️ x3	❤️ x4	❤️ x5	❤️ x7	❤️ x9	❤️ x10	❤️ x12

## Double row-laser 100w/bar



1600-2400W Can choice	1600W	1800W	2000W	2400W
Bars	16	18	20	24
Pitch/mm	2.94	2.94	2.14	2.14
Pulse Width	200	200	180	180
Energy/J	320	360	360	380
Number of people treated	👤 x18	👤 x20	👤 x24	👤 x28
Comfort Level	❤️ x11	❤️ x12	❤️ x13	❤️ x17



**USA Coherent imported  
laser bar WITH  
Certification**

**Magnetic force + fixing  
pin + curved edge teeth,  
handle head no light  
leakage and stronger**





Screen program supports customization

When adjusting the treatment parameters, you can directly input it, which is convenient and quick.

## Enter parameters directly

Improve work efficiency while quickly setting treatment parameters



1. 4 waves 1064nm +808nm + 755nm+940nm, 4 in 1 all skin type can be used

2.High power: NEW 800W / 1000W/ 1200W / 1600W / 1800W / 2000W / 2400W handle for options

3.Medical handle 4Quattro spot size 15\*25mm/15\*35mm face & body hair removal solution!

4.Cooling system: Unique Sapphire+Semiconductor+ICE+TEC cooling system, most effective to ensure machine work all day, 24hr no down time.



# Water and electricity separation design



PP cotton and resin double filters



Italy brand water pump



Extra TEC cooling



15.6 inch screen with WIFI and Bluetooth





Upgradable smart control board



Big capacitor water tank



Medical Standard power supply



The handle can be cooled up **to -15°C**, and the treatment is completely **pain-free**



**Screen linkage**

There is a **small screen behind the small handle** that can be connected to the machine screen, which is very convenient to adjust the parameters

## Product Parameters

Laser type	Diode laser
Laser wavelength	808nm or 3 wave 755&808&1064nm or 4 wave 755&808&940&1064nm
Spot size	12*12 mm2,12*20 mm2,15*27 mm2 , 12*35 mm2(optional )
Pulse width	1-300 ms (adjustable)
Energy	1-320 J/cm2 (adjustable)
Frequency	1-10 Hz(adjustable)
Language	English, Spanish, Italian, German, French, Turkish or any other language as requested
Skin type	I-VI skin type
Update system	USB / SD update
Rent System	Optional
Display	15inch' color touch LCD display



Laser module power	600W/800W/1000w/1200W/1600W/1800W/2000W/2400W
Cooling	water + air + semiconductor + A/C+TEC big cooler part
Voltage	110V/220V±20V, 50/60Hz



**Weifang KM Electronics Co., Ltd.**



13606464486



[sales@wfkmdz.com](mailto:sales@wfkmdz.com)



[wfkmdz.com](http://wfkmdz.com)

D3-H-0, D3-H-17, D3-H-18, No. 7999, East Health Street, Yongchun Community, Qingchi Street, High-Tech Zone, Weifang, Shandong, China