# Ce Certification2 in 1 3 Wavelength755/808/1064nm Hair Removal 3000w Strong Power Ice Diode Hair Removal Machine

### **Basic Information**

Minimum Order Quantity: 1 Packaging Details: box

• Delivery Time: 1-7 days

• Payment Terms: L/C,D/A,D/P,T/T,Western Union,MoneyGram

• Supply Ability: 100 set / month



### **Product Specification**

• Highlight: Ce certified hair removal machine,

3 wavelength diode hair removal, 3000w strong power beauty machine






### DIY SKIN SOLUTIONS


IPL LASER, diode LASER, ND YAG, RF, Customizable handles for versatile salon-grade treatments, like having a professional aesthetician in one device






- KM didoe laser+Yag laser feature:
  1. Germany TUV, ISO13485, ROHS, MDSAP, Australia TGA approved
- 2. No pigmentation. Suitable for any kind of skin and hairs. Safe and Fast.
- 3. Continuous working 12h: Air+water+unique designed TEC cooling system, controls steady water temperature 24, ensure machine works continuously all the day, even in summer without air-conditioner laser hair removal machine.

Free Shipping is sea transportation. Need other mode of transport, please kindly contact sales. Thank you so much. IPL / OPT / SHR / DIODE LASER / ND YAG LASER HANDLE CAN FREE Combination













Handle features of Diode laser hair removal:

- »»USA laser bar, 16 bars, high power 1600w
- »»TEC condenser cooling system: 2 big 1200W TEC condensers, keep the water constantly at 24, ensures the machine working continuously without stopping
- »» Super Cooling effect: Sapphire Temperature-5~3. Effectivly redcuce the painful in the treatment and make »» Italy Water Pump: more better for laser water circle, take away heat, longer life time.
- »»Two water filters:two food grade exchage resion,can ensure the water quality for circulation


### ND YAG LASER HANDLE:


1064nm Eliminate the black tattoo, eyebrow, eyeliner, freckles, exogenous pigmentation 532nm For treatment of red or brown tattoo, lip, eyeliner.

And effectively dilute red or brown types of shallow spots Black Carbon For deep cleaning, skin whitening, skin rejuvenation, shrink pores, acne treatment, wrinkle removal


### **IPL HANDLE:**

- \*Pigmented Lesions
- \*Skin Remodeling
- \*Tattoo Removal
- \*Acne Removal
- \*Carbon Peeling
- \*Hair Removal
- \*Vascular Therapy
- \*Wrinkle Removal





The RF handle can reduce wrinkles and firm the skin.





## Weifang KM Electronics Co., Ltd.

13606464486

sales@wfkmdz.com

wfkmdz.com

D3-H-0, D3-H-17, D3-H-18, No. 7999, East Health Street, Yongchun Community, Qingchi Street, High-Tech Zone, Weifang, Shandong, China