



High Power 2000W 808 Diode Laser 4 Wave 755 808 940 1064 Ice Titanium CE Approved Diode Laser Hair Removal Machine for Salon

Our Product Introduction

for more products please visit us on wfkmdz.com

Basic Information

- Brand Name: KM
- Model Number: 360D
- Minimum Order Quantity: 1
- Packaging Details: box
- Delivery Time: 1-7days
- Payment Terms: L/C,D/A,D/P,T/T,Western Union,MoneyGram
- Supply Ability: 100sets



Product Specification

- Applications: Permanent Hair Removal
- Cooling System: Sapphire Contact Cooling
- Fuse Specification: Ø5×25 10A
- Warrenty: 2 Years
- Power: 600W/800W/1200W/1600W/2000W
- Screen: 15 Inch Touch Screen
- Key Words: 3 / 4 Wavelength Diode Laser
- Training: User Manual+Video+face To Face
- Highlight: 2000W diode laser hair removal machine,
808nm ice titanium laser machine,
CE approved salon laser hair remover

Product Description

KM *Health Beauty* Weifang KM Electronics Co., Ltd.



*Much stable and higher powerful new golden welding laser module with USA Coherent imported laser bar WITH certification. It can shot about **20 million times** .

***Double water filters**, only change filters per 6 months and 1 year. And some old filters in some machines need change filter every month. Save much maintainance cost and times for you .

*New Italy Bluid-o-tech imported water pump replaced Chinese pump with better cooling system and more quiet duirng treatment. Those obvious difference will be found when your customers compare with some machines with Chinese water pump.

*Japan TDK Six way power supply replaced four way power supply, much higher and stable output.

*TEC cooling system, can control water temperature by yourself to keep 808 diode laser machine running continuously within 24 hours even in Summer. Same function as your A/C in your house .

*Various power laser modules for your option , 300W 500W 600W 800W 1000W 1200W 1600W ... (6bars 10basr 12bars 16bars)

*Single 808 wave, 755nm/808nm/1064nm double wave and triple wave for option.

Best cooling system:air +water+TEC semiconductor condenser

Water temperature can be controlled between 26°C—28°C,

24 hourscontinuously working.




Achieve permanent hair removal.
Hair can be easily pulled out after one treatment


3-5 cycles

Hair Removal

Safe, effective and harmless to your skin



Before



After

8 Weeks Smooth Hair Skin

1-3 weeks



Original hair loss
(3 times per week)

4-5 weeks



The hair becomes thinner
(2 times per week)

6-7 weeks



Your skin become smooth
(1 time per 2 weeks)

8 weeks & above



Say goodbye to the removal hair in repeated
(1-2 times per month)



1. Rotable handle plug, easier to install. 2.Wear-resistant tube, more durable. Handle is injection molding design, lighter and more practical. 3. Brand new 12 inch screen is clear and easy to operate. 4. Handle is injection molding design, lighter and more practical. 5.Upgrade the heat dissipation hole, the heat dissipation effect is good, and the heat dissipation is faster!

1.4000W high-power machine 2.Machine startup speed is fast 3.- 36 ° C painless treatment at freezing point
4.intelligent system 5.Fast cooling speed 5.Intelligent interconnection

>>Germany Emitter, strong energy

>>1200W power of hair removal on the whole body;

>>1-10Hz fast frequency

>> Italy water pump, it can keep machine working 24 hours without stop.

1. **Painless hair removal**, no side effect.


2. Strong power, Germany imported laser diode module, **10bar, 12 bars ,16 bars** available.

3. Big spot size **12*20 mm** or **12*35 mm**, for fast hair removal.

4. Best cooling system:air +water+TEC semiconductor condenser, Water temperature can be controlled between 26°C—28°C, 24 hours continuously working.

Automatic identification system

Correct treatment parameter will be set automatically based on spot size




Single row-laser 100w/bar



500-2000W Can choice	500W	600W	800W	1000W	1200W	1400W	1600W	1600W	2000W
Bars	5	6	8	10	12	12	16	18	20
Pitch/mm	2.94	2.94	2.94	2.94	2.94	2.14	2.14	2.14	1.96
Pulse Width	300	300	300	260	260	150	150	130	120
Energy/J	150	180	240	260	312	210	240	240	240
Number of people treated	👤 x5	👤 x7	👤 x10	👤 x12	👤 x13	👤 x14	👤 x16	👤 x18	👤 x24
Comfort Level	❤️ x2	❤️ x2	❤️ x3	❤️ x4	❤️ x5	❤️ x7	❤️ x9	❤️ x10	❤️ x12

Double row-laser 100w/bar



1600-2400W Can choice	1600W	1800W	2000W	2400W
Bars	16	18	20	24
Pitch/mm	2.94	2.94	2.14	2.14
Pulse Width	200	200	180	180
Energy/J	320	360	360	380
Number of people treated	👤 x18	👤 x20	👤 x24	👤 x28
Comfort Level	❤️ x11	❤️ x12	❤️ x13	❤️ x17

Suitable for all parts of the body



13x15mm



Vibrissa Ø8



13x20mm



13x30mm



13x25mm



13x35mm

